

Aidalarm – Mains Powered Disabled Toilet Alarm Kit

A600LKITM & A600LKITMD

The Aidalarm mains powered kit meets the requirements for emergency signalling systems for disabled persons and is fully compliant with BS8300 and the Disability Discrimination Act. Everything is provided in the kit to deliver an effective, fully compliant, simple to install and simple to use system. The controller is fitted with a volt free relay output for connection to a Multiguard Indicator such as MG212100 or a building management system if required.

How the Aidalarm Works

- The Aidalarm controller should be sited where staff are located who can respond to an emergency call.
- Ceiling pull cord and optional Dado panic strip or call button are situated in the toilet or other area where assistance may be required.
- Pulling the cord or pressing the panic strip/call button generates an immediate audible/visual alarm at both the WC and at the control panel. An LED illuminates on the pull cord giving the caller reassurance the call has been placed.
- The call can be silenced by pressing the button on the front of the control panel.
- The audible indicators at the WC will bleep every 5 seconds to re-assure the caller.
- Should the cord be pulled again while in the silenced state, the system will call again.
- Non-attendance will cause the panel to bleep every 40 seconds as a warning.
- The system can only be reset by the Press to Reset button located at or near the point of call.

Features and Benefits

- DDA & BS8300 Compliant
- Controller with High Power Piezo Sounder
- Four selectable Warning Tones
- Mains Powered with Standby batteries
- Audible & Visual Signalling to remote point
- Ceiling Pull Cord with LED
- Pull Cord Instruction Label with Braille
- Reset Button with LED, Sounder & Braille
- Overdoor Audible Visual Indication
- Relay output
- Optional Dado Panic Strip or Call Button can be added to suit requirements
- Battery powered version available
- Manufactured in the UK
- UKCA and CE marked, ROHS compliant



A600LKITM Contents

- 1 x A600L mains powered Aidalarm controller
- 1 x S1600-R Pull cord with re-assurance LED
- 1 x LAB35107 Pull Cord label with braille
- 1 x S1708A Aidalarm Reset button with re-assurance LED, sounder and braille text
- 1 x S1778A Aidalarm Overdoor light and sounder
- 6 x AA Standby batteries

Optional: S1703PY customisable call button

Add 1 x RPD01000 Dado to convert to **A600LKITMD**

