



COMPRESSION TUBE FITTINGS

As a result of tremendous efforts in research and development during the last years, with a lot of involvment in the gas analysis and gas chromatography industries with our different partners, this dead volume free compression fitting series is the best for the trace analysis industries.


FEATURES

- 316L Stainless Steel
- · Clean for UHP gas chromatography applications
- No dead volume design
- Optional surface treatment available

TYPICAL APPLICATIONS

- · Gas chromatography
- Gas analyser instruments
- Sampling system
- Flow & pressure

HOW DOES IT WORK?



The tube is inserted in a male nut and the ferrule into the body of the fitting until the tube reaches the pilot zone. The tube will not fully penetrate the pilot zone as other types of fittings does.

This particularity allows avoiding the risk of tube swelling. Such phenomenon regularly happens with other compression fittings, resulting in difficulties extracting the tube once tightened.


Its sealing point (ferrule seat) located at the right end of the tube makes a sealing edge, giving an unsurpassed type of sealing. As the cut seals the tube by the inner side of the ferrule, the outer side closes the gap on the fitting body. The male nut then pushes on the ferrule in a linear direction, preventing it from turning on the tube and damaging its seat.

Combined with a rigorous machining & cleaning quality, these series of fittings are unbeatable when measuring trace impurities as required for gas analysis industries.

www.ldetek.com

Where innovation leads to success

UNIONS & FILTERING UNIONS




| PART NUMBER | TUBE OD SIZE (INCH) | MATERIAL | OPTIONS |
|-----------------|---------------------|-----------------|---------------------------|
| LDU-1/16-SS | 1/16 | Stainless Steel | n/a |
| LDU-1/16-SS-10u | 1/16 | Stainless Steel | 10 micron press in filter |
| LDU-1/16-SS-SC | 1/16 | Stainless Steel | Sulfinert coating |

REDUCING UNIONS




| PART NUMBER | TUBE OD SIZE (INCH) | TUBE OD SIZE (INCH) | MATERIAL | OPTIONS |
|-------------------------|---------------------|---------------------|-----------------|---------------------------|
| LDRU-1/8 to 1/16-SS | 1/8 | 1/16 | Stainless Steel | n/a |
| LDRU-1/8 to 1/16-SS-10U | 1/8 | 1/16 | Stainless Steel | 10 micron press in filter |
| LDRU-1/8 to 1/16-SS-SC | 1/8 | 1/16 | Stainless Steel | Sulfinert coating |






| PART NUMBER | TUBE OD SIZE (INCH) | MATERIAL | OPTIONS |
|----------------|---------------------|-----------------|-------------------|
| LDC-1/16-SS | 1/16 | Stainless Steel | n/a |
| LDC-1/16-SS-SC | 1/16 | Stainless Steel | Sulfinert coating |

TEES





| PART NUMBER | TUBE OD SIZE (INCH) | MATERIAL | OPTIONS |
|----------------|----------------------------|-----------------|-------------------|
| LDT-1/16-SS | 1/16 | Stainless Steel | n/a |
| LDT-1/16-SS-SC | 1/16 | Stainless Steel | Sulfinert coating |








| PART NUMBER | TUBE OD SIZE (INCH) | MATERIAL | OPTIONS |
|-----------------|---------------------|-----------------|-------------------|
| LDSN-1/16-SS | 1/16 | Stainless Steel | n/a |
| LDSN-1/16-SS-SC | 1/16 | Stainless Steel | Sulfinert coating |
| LDSN-1/8-SS | 1/8 | Stainless Steel | n/a |
| LDSN-1/8-SS-SC | 1/8 | Stainless Steel | Sulfinert coating |

FERRULES






| PART NUMBER | TUBE OD SIZE (INCH) | MATERIAL | OPTIONS |
|----------------|---------------------|-----------------|-------------------|
| LDF-1/16-SS | 1/16 | Stainless Steel | n/a |
| LDF-1/16-SS-SC | 1/16 | Stainless Steel | Sulfinert coating |
| LDF-1/8-SS | 1/8 | Stainless Steel | n/a |
| LDF-1/8-SS-SC | 1/8 | Stainless Steel | Sulfinert coating |






| PART NUMBER | TUBE OD SIZE (INCH) | MATERIAL | OPTIONS |
|-----------------|---------------------|-----------------|-------------------|
| LDLN-1/16-SS | 1/16 | Stainless Steel | n/a |
| LDLN-1/16-SS-SC | 1/16 | Stainless Steel | Sulfinert coating |

CAPS






| PART NUMBER | TUBE OD SIZE (INCH) | MATERIAL | OPTIONS |
|-------------|---------------------|-----------------|---------|
| LDC-1/16-SS | 1/16 | Stainless Steel | n/a |






| PART NUMBER | TUBE OD SIZE (INCH) | MATERIAL | OPTIONS |
|----------------|---------------------|-----------------|-------------------|
| LDP-1/16-SS | 1/16 | Stainless Steel | n/a |
| LDP-1/16-SS-SC | 1/16 | Stainless Steel | Sulfinert coating |

ADAPTER 10-32





| PART NUMBER | TUBE OD SIZE (INCH) | MATERIAL | OPTIONS |
|--------------------|---------------------|-----------------|-------------------|
| LDA1032-1/16-SS | 1/16 | Stainless Steel | n/a |
| LDA1032-1/16-SS-SC | 1/16 | Stainless Steel | Sulfinert coating |





| PART NUMBER | NPT SIZE (INCH) | TUBE OD SIZE (INCH) | MATERIAL | OPTIONS |
|-----------------------|-----------------|---------------------|-----------------|-------------------|
| LDANPT-1/8-1/16-SS | 1/8 | 1/16 | Stainless Steel | n/a |
| LDANPT-1/8-1/16-SS-SC | 1/8 | 1/16 | Stainless Steel | Sulfinert coating |