



Haven Automation Limited

Calibration Solutions for Industry

Measurement House, Kingsway,
Fforestfach, Swansea SA5 4EX, UK.
Tel: General: +44 (0) 1792 588722
Sales: +44 (0) 1792 580255
Service: +44 (0) 1792 579696
Fax: +44 (0) 1792 582624
Email: mail@haven.co.uk
Web: www.haven.co.uk

Fluidised Baths - BFS High Temperature Bath



- Temperature range 200°C to 1100°C
- Control stability $\pm 0.5^\circ\text{C}$ to $\pm 3.5^\circ\text{C}$

Designed for applications requiring a constant high temperature source for calibration. The BFS is supplied with a TC-5 temperature controller, a separate air supply control unit which incorporates two flowmeters for monitoring the air supply, a charge of fluidising medium (aluminium oxide) and air diffuser (zirconium oxide).

The BFS has a hinged lid and a cylindrical bath. Substantial firebrick insulation is incorporated within the outer container and the lid. The inner container holds a layer of zirconium oxide, which acts as a heat insulator and a layer of aluminium oxide, the fluidising medium. The inner container is divided into inner and outer fluidised sections. Each area has a separate air supply which must be oil, water and dust free.

The air supply is adjustable to obtain uniform fluidisation in both sections of the bath. Heaters are mounted in the firebrick insulation between the inner and outer container; heat is radiated inwards to the fluidised bath.

An air extraction tube enables dust created by the bath's operation to be removed if connected to an extraction duct or fan. The dust can also be trapped in a small tank of water.

The TC-5 is used for setting, controlling and indicating the bath temperature. The TC-5 uses a chromel/alumel thermocouple, which mounts onto the back of the BFS and fits into the pocket of the inner container and is also fitted to the air flow control unit.

BFS with TC-5 Temperature Controller	
Temperature Range °C	200 to 1100
Temperature Stability °C (short term)	± 0.5 to 3.5
Display Resolution °C	1
Type of Control	3 term (PID) digital set/readout
Sensor Type	K Chromel/alumel thermocouple
Air Pressure, kPa (psi)	47 (7)
Maximum Flow, litres/min	85
For immersed object: Maximum load size Maximum surface area	2.2 litres 1080mm ²
Weight of Medium, kg	16kg (aluminium oxide) 16.8kg (zirconium oxide)
Overall Size L x W x H, mm	686 x 686 x 876 (airflow controller adds 305mm to the width)
Working Volume, Diameter x Depth, mm	203 x 203 Top lid has a central opening 82.5mm square
Overall Size L x W x H, mm (TC-5)	430 x 305 x 140

